## **HREAL® 6100 PLUS**

the new electric wheelchair for indoor use with narrow chassis









# Freedom of movement and freedom of choice with REAL 6100 PLUS

Having weak legs you need a versatile chair to enable you to be active whilst seated to improve independence at home, work or in school.

This places stringent demands on function and quality. The chair must be comfortable, provide an ergonomically correct sitting position and enable you to move around in your chosen environment.

#### Freedom of movement

The REAL 6100 PLUS is a powered wheelchair for indoor use. It is built to give the user maximum freedom of movement at home, at work or at school.

The wheelchair will enable you to move around easily in confined spaces as the chassis is only 570 mm wide. The electric height adjustment has an impressive 280 mm range and will lift 750 mm off the floor enabling the user to reach heights normally out of a seated person's range.

The mid-wheel drive enables the REAL 6100 PLUS to turn on its own axis and the individual wheel suspension allows it to climb obstacles up to 40 mm.

## Freedom of choice in accordance of the user's needs

The REAL 6100 PLUS has great potential for adjustment to suit the user's needs and wishes. The standard

version of the REAL 6100 PLUS has an ergonomic seating system and foldable armrests making it a very comfortable chair, easy to transfer in and out of.

The leg support has a stable footplate with a length and angle adjustment.

## Wide range of accessories and alternatives

The REAL 6100 PLUS can be equipped with a wide range of alternatives and accessories. You can choose between various types of tilt in space, alternative seats and back rests, etc. For more information please see our accessories brochure.

We are also proud to offer Dynamic Controls' range of electronic accessories for even better individual adaptation. For more information please see <a href="http://www.dynamiccontrols.com/designers-and-manufacturers/products">http://www.dynamiccontrols.com/designers-and-manufacturers/products</a>





## A system where your needs dictate the

### design







#### **TECHNICAL DATA**

Max user weight
Top speed
Turning space180°
Driving wheel
Driving time per charge
Obstacle ability
Weight
Charging time
Charger tested and approved by
Mercado Medic AB
Batteries tested and approved by
Mercado Medic AB

135 kg 4,5 km/h 820 mm Both center wheels approx. 15 km 40 mm 76 kg incl. batt. approx. 6-8 hours

Mentzer 3A

Sonnenschein 2st 12V 25 Ah

#### STANDARD MEASUREMENTS

 Total width
 570 mm

 Length
 800 mm

 Wheel front/back
 Ø 125 mm

 Driving wheel
 Ø 210 mm

 Seat height\*
 470-750, 400-600 mm

 Leg support length
 370-530 mm

 Seat width
 400-480 mm

Seat width 400-480 mm Seat depth 390-480 mm

Seattilt -15° +8°, -8° +15°, 0° +23° Back support height 330-430 mm

Back support height 330-430 mm Back support angle -15-+45°

\* Measured without seat angle from floor to underside of seat, with seat in flat position. With seat tilt +1 cm. With seat tilt "adjustable reinforced seat frame" +2 cm.

#### PROGRAMMING DEVICE

Programmable functions:

- Forward speed
- Forward acceleration
- Forward deceleration
- Reverse speed
- Reverse acceleration
- Reverse deceleration
- Turning speed
- Turning acceleration
- Turning deceleration
- Joystick sensitivity
- Reversed joystick function
- Use of external joystick

CE

